

# Pressure S-Class Improvement

## Hart7 Firmware and Reference Accuracy

### Improved Accuracy

- ◆ Improved reference accuracy available for Cerabar S and Deltabar S
- ◆ **Standard** reference accuracy up to  $\pm 0.05\%$  and **Platinum** reference accuracy up to  $\pm 0.025\%$  for Cerabar S - PMP71 and PMC71
- ◆ **Standard** reference accuracy  $\pm 0.05\%$  and **Platinum** reference accuracy up to  $\pm 0.035\%$  for Deltabar S – PMD75



### New Firmware HART7

- New **HART 7** version: 02.20.zz, DevRev022 available for all pressure S-Class devices
- **32 character tag** - ensures a clear identification of the device
- All Variables with **Status** – ensures safe and reliable operation
- **Digital Loop Check** - ensures safe and reliable operation
- Local Interface **Lock** – ensures safe operation
- 16- bit Manufacturer ID

